



TECHNICAL DATA SHEET

Varn® Sunday Fount KT10-5SF

Description:

Extensive research and development in the interaction of fount and ink at high speeds i. e. >15 mp/s, resulted in the development of Sunday Fount which is specially formulated to meet the exacting demands of modern large format high speed Heatset Web Offset Presses and also meet the demands of modern plate technology including CtP and is compatible with the majority of negative and positive (baked) plates.

Application:

- Heidelberg Sunday and ManRoland Goss M-Series presses
- Compatible with dayGraphica sleeves
- Recommended dosage between 2.00% and 4.00% concentration to reach pH 4.5 - 5.5, depending on local water conditions.

Key Features:

- Classified as Non-Hazardous for safer handling and storage conditions.
- Dynamic surface tension properties which give the printer the latitude normally associated with alcohol but without any environmental risks.
- Effective ink/water balance.
- Extremely clean running fount solution, minimising ink feedback onto dampers and into re-circulating tanks.
- Fewer blanket washes resulting in reduced down time and waste.
- Eliminates piling.
- Compatible with the majority of inks, stocks and water conditions
- Flashpoint (>100°C)

For more details, contact your nearest Flint Group Packaging Solutions office or dealer.

Flint Group Packaging Solutions
www.flintgrp.com
info@flintgrp.com

DISCLAIMER

The aim of our technical documents is to inform and advise our customers. The information provided herein is correct to the best of Flint Group's knowledge. No liability for any errors, facts or opinions is accepted. Customers/Users must always make every effort to ensure that the products employed are suitable and appropriate for the purpose intended. No responsibility for any loss as a result of any person placing reliance on any material contained herein will be accepted.

Product names followed by ® are trademarks registered by Flint Group.

Version: 17/05/2026



TECHNICAL DATA SHEET

Varn® Sunday Fount KT10-5SF

Storage:

- The products should be processed within 12 months after production date.
- To prolong the shelf life of the fount concentrate, we recommend storing the product in its original, un-opened packaging at room temperature (20 - 25°C), as correct storage conditions are essential.

Quality / Environment / Health & Safety

Flint Group maintains a comprehensive Management System that integrates quality, environment, health & safety. Our production and quality control processes meet high industry standards, ensuring product safety and reliability. When used as intended, our products are safe and pose no hazards under normal conditions. For more details, refer to the Safety Data Sheet.

Handling precautions – skin sensitization

Ensure the use of proper protective equipment when handling chemicals. For detailed guidance, refer to the Safety Data Sheet and consult with your PPE (Personal Protective Equipment) provider.

Additional Information

Please contact your local Flint Group Customer/Technical Service if further information is required.

For more details, contact your nearest Flint Group Packaging Solutions office or dealer.

Flint Group Packaging Solutions
www.flintgrp.com
info@flintgrp.com

DISCLAIMER

The aim of our technical documents is to inform and advise our customers. The information provided herein is correct to the best of Flint Group's knowledge. No liability for any errors, facts or opinions is accepted. Customers/Users must always make every effort to ensure that the products employed are suitable and appropriate for the purpose intended. No responsibility for any loss as a result of any person placing reliance on any material contained herein will be accepted.

Product names followed by ® are trademarks registered by Flint Group.

Version: 17/05/2026