

ABB MEASUREMENT & ANALYTICS | DATA SHEET

LGR-ICOSTM GLA151-N2OM1 $N_2O \& CH_4$ analyzer – QC Portable



Highly sensitive and accurate analyzer for reliable measurement of N_2O and CH_4 .

Measurement made easy

LGR-ICOS™ GLA151-N2OM1 N₂O & CH₄ – Quantum cascade portable analyzer

Features and benefits

- Simultaneous measurements of N₂O and CH₄
- High precision and robust to cross-interferences
- Measurement rates selectable up to 1 Hz
- Installed and operational in minutes
- Extremely high dynamic range
- Unsurpassed ruggedness and reliability
- Real-time diagnostics

Overview

The ABB LGR-ICOS gas analyzers build on the heritage and extensive track record of Los Gatos Research analyzers, using patented Off-Axis Integrated Cavity Output Spectroscopy (OA-ICOS) technology, the latest evolution in tunable diode laser absorption spectroscopy (TDLAS).

The GLA151-N2OM1 quantum cascade (QC) portable analyzer simultaneously measures water vapor mole fraction. As a result, the analyzer reports N_2O and CH_4 on a dry mole basis. It accurately corrects for water vapor dilution and absorption line broadening effects without the need for sample drying or empirical corrections.

The GLA151-N2OM1 analyzer is designed for the most demanding field applications, as proven by its track record, and generally focused on greenhouse gases emission studies and atmospheric monitoring, where highest precision, accuracy, ruggedness and mobility are required.

... Overview

ABB's patented OA-ICOS technology, a fourth-generation cavity enhanced absorption technique, has many advantages over older conventional and delicate cavity ringdown spectroscopy and direct absorption techniques. OA-ICOS analyzers are simpler, easier to operate and more rugged. They exhibit negligible zero and span drift and a significantly reduced need for regular calibration with expensive reference gases. As a result, ABB analyzers provide higher performance and reliability with minimal operationnal cost.

The GLA151-N2OM1 has an internal computer that can store data practically indefinitely (for applications requiring unattended longer term operation), and send real-time recordings to a data logger through its analog and digital (RS232) outputs. The analyzer includes control and analysis software.

Accessories

MIU-16	Multiport Inlet Unit Automated control of up to 16 inlet ports	
MIU-8	Multiport Inlet Unit Automated control of up to 8 inlet ports	
ACC-DP3H	3-head Diaphragm External Pump	
OPT-DATALOG	Digital Data Logging Capability Multi-channel data logging option records and synchronizes serial (RS-232) outputs from multiple ABB analyzers and other devices (GPS, anemometers)	

Ordering information

• LGR-ICOS™ GLA151-N2OM1

N₂O & CH₄ analyzer – QC portable

Specifications

Precision (1o, 1 sec / 10 sec):

N ₂ O: 0.5 ppb / 0.2 ppb	[<500 ppb]
CH₄: 2 ppb / 0.6 ppb	[<500 ppb]
H ₂ O: 50 ppm / 20 ppm	

Linear measurement ranges (meets all specifications):

 N_2O : Up to 4 ppm CH₄: Up to 100 ppm H₂O: Up to 30 000 ppm

Operational ranges:

 N_2O : Up to 40 ppm CH₄: Up to 600 ppm H₂O: <99% RH, non-condensing

Measurement rate:

0.01 – 1 Hz (user selectable)

Flow response time:

<30 seconds (1/e) <10 seconds (1/e) with external diaphragm pump ACC-DP3H

Sampling conditions:

Operating temperature: 5 – 45 °C Ambient humidity: <99% relative humidity non-condensing

Data outputs:

WiFi, Ethernet, USB, Serial (RS-232)

Power requirements:

24-30VDC 110/240 VAC, 50/60 Hz 180 watts (steady state) max 300 watts with ACC-DP3H

Dimensions:

51 cm (20 in.) x 61cm (24 in.) x 20 cm (8 in.)

Weight:

23 kg (51 pounds)

ABB Inc. Measurement & Analytics 3400, Rue Pierre-Ardouin Quebec, Quebec Canada GIP 0B2 Tel: +1 418 877-2944 Email: icos.sales@ca.abb.com

abb.com/analytical

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB CA does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB CA. Copyright© 2021 ABB All rights reserved